



## Standard Barrel Copper Lug

**T&B Catalog Number:**

53233L

**UPC Number:**

78621070706

**Status:**

Active

**Description:**

Cast Copper Two-Hole Heavy Duty Lug - Straight Standard Barrel - max 35KV, 1500 kcmil Wire, 1/2 Bolt Size, 1 3/4 in. Hole Spacing, Tin Plated Blind End, 150

### Features

Electro Tin-Plated for Corrosion Resistance. Chamfered Barrels Provide Ease of Strand Entry and Inspection hole facilitates full insertion of the conductor.

Cable Area Clearly Identified on Lug.

### General



Style	Heavy-Duty
Material	Cast Copper
Finish	Tin Plated
Wire Size	1500 kcmil
Number of Studs	2
Stud Size (inches)	1/2
Bolt Hole Spacing	1 3/4
Tongue Angle	Straight
Barrel Length	Standard
Barrel Shape	Standard
Tongue Width	Standard
Peep Hole	N
Marking	Standard
Hole Shape	Round
Die Code	150

### Dimension Information

A (inches)	7 5/16
B (inches)	3 1/8
C (inches)	2
D (inches)	1/2
E (inches)	1 7/8
F (inches)	5/8
H (inches)	1 3/4

### Specifications

Temperature Rating	105°C
Voltage Rating	600V to 35KV

### Tooling

Connector & Tooling Chart	Available on Website
---------------------------	----------------------

### Packaging

Package in Units	3
T&B Sold in UOM	Each
T&B Weight Per UOM	2.5 lbs. Each

### Application Support

Overview	Available on Website
----------	----------------------

## Notes

Dimensions given for reference only. Dimensions may vary up to +/- .030.

## Certifications

RoHS Compliance Yes

## Certifications



File Nbr:  
E9809

### For further technical assistance, please contact us...

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
www.tnb.com

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email:techsupport@tnb.com