



Armored Cable/Flexible Metal Conduit Fittings

T&B Catalog Number:

328

UPC Number:

78621000328

Status:

Active

Description:

1 1/2 Inch. Tite-Bite 90 Degree Connector, Malleable Iron-Electro Zinc Plated.

Features

The angle clip gives secure mechanical grip that tightens under tension or vibration

Throat is long enough to install in cast housing knockouts.

Application

For use with Armored Cable and Flexible Metal Conduit.

To connect and effectively bond armored cable or flexible metal conduit to a box or an enclosure.

General

Trade Size (inches)

1 1/2

Material

Malleable Iron

Finish

Electro Zinc Plated

Dimension Information

Dimension A (inches)

4 1/8

Dimension B (inches)

4 1/8

Knockout Size (inches)

1 1/2

Cable Opening-Minimum (inches)

1.812

Cable Opening-Maximum (inches)

2.031

Specifications

3dmodel

Available on Website

Packaging

T&B Inner Pack

1

Package in Units

10

T&B Sold in UOM

Each

T&B Weight Per UOM

196.5 lbs. per 100

Notes

U.L. Listed for flexible metal conduit only.

Certifications

RoHS Compliance

No

Certifications



File Nbr:

E 23018

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125

T&B Technical Support
MS 3B-50
8155 T&B Blvd.

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289

