



Rigid/IMC Conduit Fittings

T&B Catalog Number:

1353

UPC Number:

78621001353

Status:

Active

Description:

Pipe Spacer, Malleable Iron-Hot Dipped Galvanized, use with conduit sizes of 3 1/2 in.-4 in.. For use with Rigid/IMC Conduit.

Features

Used with T&B conduit straps to permit space between conduit and mounting surface.

Eliminates need for costly offset-bending conduit and possible corrosive moisture traps when conduit is mounted directly to a surface.

Premountable and stackable to eliminate offsetting.

Application

Provides mounting surface for conduit where installation requires air space between conduit and supporting surface.

General

Material	Malleable Iron
Finish	Hot-Dipped Galvanized
Screw Size	#14

Dimension Information

Size (inches)	3 1/2 - 4
Dimension A (inches)	7 9/16
Dimension B (inches)	2
Conduit Size (inches)	3 1/2 - 4

Packaging

Package in Units	10
T&B Sold in UOM	Each
T&B Weight Per UOM	50 lbs. per 100

Notes

Conforms to NEC 300-5-C

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com