# Thomas&Betts







RC717

**UPC Number:** 78621082010

Status: Active

**Description:** 

Insulated Vinyl Ring Terminal For Wire Range 12-10 Stud Size 1/4, Yel-


۷	۷	E	В	ι	JŞ	S	E

http://www-public.tnb.com/contractor/docs/ US Cutsheet PDF Catalog Link

stakon.pdf

**Features** 

These terminals are self-insulated with a PVC insulation sleeve of extra length to give protection and relieve bending stress at wire's flex point. Brazed seam barrel is serrated to obtain high pull-out value.



General	
Insulation Type	Insulated Vinyl
Terminal Series	RC
Material	Copper
Finish	Electro -Tin Plated
Color	Yellow
Wire Range	12-10
Stud Size	1/4

Dimension Information		
Maximum Insulation (inches)	.210	
Stock Thickness	.04	
A (inches)	1.16	
B (inches)	.50	
C (inches)	.27	
M (inches)	.90	
Specifications		

-p	
Temperature Rating	105°C
Voltage Rating	600V
Flammability Rating	UL 94 V-0

	,
Tooling	

Tool Charts	Available on Website
Application Tools	WT145C, WT2000, WT112M, ERG4001, ERG4003
Recommended Tool	ERG4001
Packaging	
TOD Order Multiple	500
T&B Order Multiple	500
T&B Inner Pack	500
Package in Units	5000
Package Type	Bulk
T&B Sold in UOM	Each
T&B Weight Per UOM	0.53 lbs. per 100

# **Application Support**

Alternate Package Qty

Overview	Available on Website
Wire Guide Tables	Available on Website

10RC-14



### **Notes**

Most terminals can be put on Mylar Tape for reel fed applications by adding the suffix M to the bulk catalog numbers.

# Certifications

RoHS Compliance

Yes

# Certifications





File Nbr: E9809

### For further technical assistance, please contact us...

T&B Technical Support MS 3B-50 8155 T&B Blvd. Memphis, TN 38125 Hours: 7AM - 6PM CDT Monday-Friday Phone: (888) 862-3289 Fax: (901) 252-1321 Email:techsupport@tnb.com

Thomas & Betts - USA 8155 T&B Blvd. Memphis, TN 38125 www.tnb.com