



Aluminum Lug
T&B Catalog Number:

ALS60
 78378605091
 Active

UPC Number:
Status:
Description:

Aluminum Two-Hole Lug - Straight Long Barrel, Wire Range 900 54/7, 954 45/7 ASCR, 1000-1033 Str., 1033 Compact, 1/2 Inch Bolt Size, Blind-End, Hydraulic Dies: 1 1/2, 6024, 125H, CSA 30

Features

Complete die and crimp information clearly indented on each lug. Install with standard tools and dies.
 NEMA standard mounting holes. Use 1/2 inch mounting hardware for all sizes.
 Prefilled with oxide inhibitor.

General

Style	ALS
Material	Aluminum
Conductor Range - ASCR	900 54/7, 954 45/7
Conductor Range - Stranded	1000-1033
Conductor Range - Compact	1033

Dimension Information

Length (inches)	7 1/4
Width (inches)	1 5/8
T (inches)	5/8
Diameter Min. (inches)	1.172
Diameter Max. (inches)	1.151

Tooling

Hydraulic Dies	1 1/2, 6024, 125H, CSA 30
----------------	---------------------------

Packaging

Package in Units	20
T&B Sold in UOM	Each
T&B Weight Per UOM	74.5 lbs. per 100

Notes

For aluminum conductor only.
 Hole Spacing 1 3/4 inches.
 Available tin-plated (add suffix P to catalog number).

Certifications

RoHS Compliance	Yes
-----------------	-----

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
 www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email:techsupport@tnb.com