



**Fork Terminal**  
**T&B Catalog Number:**

RC10-14F  
 78621080443  
 Active

**UPC Number:**  
**Status:**  
**Description:**


Insulated Nylon Fork Terminal For Wire Range 12-10 Stud Size 1/4, Yellow

**WEB\_USE**

US Cutsheet PDF Catalog Link <http://www-public.tnb.com/contractor/docs/stakon.pdf>

**Features**

Inner bronze insulation grip sleeve lengthens flex radius of conductor and eliminates conductor creep. Nylon jacket is color-coded.



**General**

Insulation Type	Insulated Nylon
Terminal Series	RC
Material	Copper
Finish	Electro -Tin Plated
Color	Yellow
Wire Range	12-10
Stud Size	1/4

**Dimension Information**

Maximum Insulation (inches)	.210
Stock Thickness	.04
A (inches)	1.12
B (inches)	.50
C (inches)	.27
M (inches)	.86

**Specifications**

Temperature Rating	105°C
Voltage Rating	600V
Flammability Rating	UL 94 V-2

**Tooling**

Tool Charts	Available on Website
Application Tools	WT145C, WT2000, WT112M, ERG4001, ERG4003, WT145A
Recommended Tool	ERG4001

**Packaging**

T&B Order Multiple	50
T&B Inner Pack	50
Package in Units	250
Package Type	Standard
T&B Sold in UOM	Each
T&B Weight Per UOM	6.25 lbs. per 1000
Alternate Package Qty	RC1163

**Application Support**

Overview	Available on Website
Wire Guide Tables	Available on Website

## Certifications

RoHS Compliance Yes

## Certifications



File Nbr:  
E9809

### For further technical assistance, please contact us...

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
www.tnb.com

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email:techsupport@tnb.com