


4-11/16 in. Square Boxes


Conduit Knockouts



Cat. No.	Volume (Cu. in.)	Features		Knockouts				
		Bracket	Raised Ground Screw	1/2 in. sides	1/2 in. bottom	3/4 in. sides	3/4 in. bottom	1 in. sides
1-1/2 in. Deep								
CI72151-K	30.0	-	yes	10	4	6	2	-
BC73151-K	30.0	-	-	10	-	6	-	-
2-1/8 in. Deep								
CI72171-1	42.0	-	yes	-	4	2	2	6
BC72171-K	42.0	-	yes	10	4	6	2	-
CI72171-KSB	42.0	"SB"	yes	8	4	2	2	-
CI72171-KSSX	42.0	"SSX"	yes	4	4	4	2	-
CI72171-1-SSX	42.0	"SSX"	yes	-	4	2	2	4
BC73171-K	42.0	-	-	10	-	6	-	-

4-11/16 in. Square Boxes

Covers



Cat. No.	Description
Flat Covers	
BC72-C-1	Blank
BC72-C-6	With concentric 1/2 in. and 3/4 in. conduit knockout
Single Device Covers	
CI72-C-10	Raised 1/8 in. (1.7 cu. in.)
CI72-C-13	Raised 1/2 in. (4.3 cu. in.)
CI72-C-14	Raised 3/4 in. (6.2 cu. in.)
Two Device Covers	
BC72-C-17	Raised 1/2 in. (6.4 cu. in.)
Adaptors	
CI72-A-52	To install 4 in. square covers on 4-11/16 in. square boxes. Raised 1/4 in. (3.0 cu. in.)