

**Splice Connector**  
**T&B Catalog Number:**

54806

**UPC Number:**

78621054806

**Status:**

Active

**Description:**Copper Two-Way Splice - Long Barrel for 4 AWG, 91/24 Die Code 29  
Gray**Features**

Two-way connectors provide high pullout values, are easy to insulate and provide a low-resistance connection of high quality and low installed cost.

**General**

Style	Two-Way Long Barrel Splice
Material	Copper
Finish	Tin-Plated
Wire Size	#4 AWG
Wire Size Flex	91/24 = 36.7 kcmil
Die Color	Gray
Die Code	29

**Dimension Information**

A (inches)	1.75
E (inches)	0.39

**Specifications**

Voltage Rating	600V
----------------	------

**Packaging**

T&B Inner Pack	50
Package in Units	500
T&B Sold in UOM	Each
T&B Weight Per UOM	3 lbs. per 100

**Application Support**

T&B Instruction Sheets	ta00674-tb2
------------------------	-------------

**Certifications**

RoHS Compliance	Yes
-----------------	-----

**Certifications**

File Nbr:

Y

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
www.tnb.com

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email:techsupport@tnb.com