



RCC600E

by Burndy Catalog ID: RCC600E

Ratchet Cable Cutting Tool, 600 kcmil Soft Drawn Copper, 600 kcmil Aluminium, Maximum insulation dia. 1.05 in, Handles:Anti-Slip Rubber over high strength, High strength steel blades and frame

- Patented high strength steel blades
- Quick release, bi-directional ratchet mechanism
- Rapid blade advance

1 year limited warranty (excluding blades)

Product Details

General

Operation	Ratchet mechanism includes emergency release feature
Tool Type	Ratchet Cutters for Cu/Al
Туре	Cutters
UPC	781810488195
UPC 12 Digit	7818104881955

Dimensions

Cable Insulation Diameter Maximum	1.050 in
Length	10.5 in
Weight	1.2 lb
Width	1.25 in

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1	
-		

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday Emergency Service 24-hours/365 Days Phone: 1-800-346-4175 1-603-647-5299 (International)