



Liquidtight Flexible Metal Conduit Fittings

T&B Catalog Number:

5353GR

UPC Number:

78621090009

Status:

Active

Description:

3/4 Inch external bonding liquidtight insulated connector flexible metal conduit fitting, 90 Degree Angle, with Revolver? lug, with tin-plated copper alloy lug for AWG #14-#2 ground wire, for use in wet locations, 10 pieces

Features

Ability to install quickly with low torque effort

Application

To positively bond conduit to box or enclosure

General

| | |
|---------------------|--------------------------------------|
| Trade Size (inches) | 3/4 |
| Material | Malleable Iron |
| Finish | Electro Zinc Plated/Chromate Coating |
| Ground Wire | 14-4 |

Dimension Information

| | |
|----------------------|---------|
| Dimension A (inches) | 1 21/32 |
| Dimension B (inches) | 1 13/16 |
| Dimension C (inches) | 9/16 |

Specifications

| | |
|---------|----------------------|
| 3dmodel | Available on Website |
|---------|----------------------|

Packaging

| | |
|--------------------|--------------------|
| T&B Inner Pack | 10 |
| Package in Units | 50 |
| T&B Sold in UOM | Each |
| T&B Weight Per UOM | 42.31 lbs. per 100 |

Certifications

| | |
|-----------------|-----|
| RoHS Compliance | Yes |
|-----------------|-----|

Certifications



File Nbr:

E 3060

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com