



Fork Terminal
T&B Catalog Number:

18RA-10F
 78621080093
 Active

UPC Number:
Status:
Description:

Insulated Vinyl Fork Terminal For Wire Range 22-16 Stud Size #10, Red
WEB_USE

US Cutsheet PDF Catalog Link <http://www-public.tnb.com/contractor/docs/stakon.pdf>

Features

These fork terminals have extra-long PVC insulation sleeve for protection and stress relief at wire's flex point. Brazed seam barrel is serrated for high pull-out value. Insulation is color-coded.

General

| | |
|-----------------|---------------------|
| Insulation Type | Insulated Vinyl |
| Terminal Series | RA |
| Material | Copper |
| Finish | Electro -Tin Plated |
| Color | Red |
| Wire Range | 22-16 |
| Stud Size | #10 |

Dimension Information

| | |
|-----------------------------|------|
| Maximum Insulation (inches) | .150 |
| Stock Thickness | .03 |
| A (inches) | .97 |
| B (inches) | .31 |
| C (inches) | .27 |
| M (inches) | .81 |

Specifications

| | |
|---------------------|-----------|
| Temperature Rating | 105°C |
| Voltage Rating | 600V |
| Flammability Rating | UL 94 V-0 |

Tooling

| | |
|-------------------|--|
| Tool Charts | Available on Website |
| Application Tools | WT145C, WT2000, WT112M, ERG4001, ERG4003 |
| Recommended Tool | ERG4001 |

Packaging

| | |
|-----------------------|-------------------|
| T&B Order Multiple | 100 |
| T&B Inner Pack | 100 |
| Package in Units | 500 |
| Package Type | Standard |
| T&B Sold in UOM | Each |
| T&B Weight Per UOM | 0.25 lbs. per 100 |
| Alternate Package Qty | RA1157 |

Application Support

| | |
|-------------------|----------------------|
| Overview | Available on Website |
| Wire Guide Tables | Available on Website |

Certifications

RoHS Compliance Yes

Certifications



File Nbr:
E9809

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com