



## Liquidtight Flexible Cord & Cable Fittings

### T&B Catalog Number:

2565

### UPC Number:

78621002565

### Status:

Active

### Description:

1-1/2 in. straight malleable iron liquidtight strain relief cord connector, cord range-1.375-1.625.

### Application

Suitable for use in hazardous locations where general purpose equipment is specifically permitted by NEC 501-4(b).

Meets Coast Guard CG293

### General

Material Malleable Iron

### Dimension Information

Hub Size (inches)	1 1/2
Dimension A (inches)	2 13/16
Dimension B (inches)	2 5/8
Dimension C (inches)	13/16
Cord Range (inches)	1.375-1.625
Throat Diameter (inches)	1 29/64

### Specifications

3dmodel	Available on Website
Temperature Rating	105 C

### Packaging

Package in Units	5
T&B Sold in UOM	Each
T&B Weight Per UOM	102 lbs. per 100

### Application Support

Product Overview	Available on Website
Specifications	Available on Website
Portable Cord Selection Table	Available on Website

### Notes

Remove sufficient outer covering of cable to permit conductors to pass thru connector body.

### Certifications

RoHS Compliance	Yes
-----------------	-----

### Certifications



File Nbr:  
E 13938

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
www.tnb.com

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321

