#### MSR-C2



**SM002A** 



**S102WD** 



# **Accessories**

## **Stainless Steel Sealing Rings**

Cat. No.	Description
MSR-C2	Stainless steel sealing ring, tamper-proof
SM002A	Screw on type, tamper resistant

### **Polycarbonate Sealing Ring**

Cat. No.	Description
S102WD	Ring, available with any meter socket

When ordering any meter socket, add suffix "Z" to meter socket cat. no. to exchange standard stainless steel ring for S102WD model.

# **Meter Protectors**

## **Product Specifications**

- Meter protector for use in problem areas (trailer parks, playgrounds, conservation areas)
- Steel construction (16 ga. galv. steel)
- Clear, unbreakable polycarbonate front cover, which allows full view of meter revenue reading and serial number
- Sealing and padlocking provision
- Grey painted

Cat. No.	Description
MP01	7-1/6 in. dia. x 4-3/4 in. deep for use with single phase residential meters
MP02	7-1/6 in. dia. x 8-3/4 in. deep for use with all meters, other than single phase residential meters

# **Accessories**



#### BS087 / BS089 / BS090



**CM-BS100** 



LS500



MH200





MH10X



#### **Blank Meter Cover Plates**

Cat. No.	Description
BS087	Grey ABS
BS089	Plastic "throw-away" cover
BS090	Clear unbreakable polycarbonate

## **Jumper Bar**



Cat. No.	Description	
CM-BS100	200 A Max.	

# **Meter Jaw Safety Shroud**

Cat. No.	Description	
LS500	Red polycarbonate, 100/200 A	

## **Mast Coupler**



Cat. No.	Description
MH200	Fits all sockets with regular 2-1/2 in. hub opening

## **Masts Coupler**



Cat. No.	PVC Cat. No.	A Hub Size (in.)	В
MH10X	_	1	
MH12X	PH12	1-1/4	For 2-1/2 in. regular hub opening
MH15	PH15	1-1/2	(add hub adapter plate BS052 if used
MH20	PH20	2	with units having 4 in. hub openings)
MH25	PH25	2-1/2	
MH30	<u> </u>	3	
MH35	_	3-1/2	For 4 in. hub opening
MH40	_	4	

Supplied with 4 Robertson head screws.

## **Hub Adapter Plate**



Cat. No.	Description
BS052	Permits use of regular size hubs on larger hub openings













Consist of thermoplastic insulators with jaws and connectors assembled for replacement of one meter socket

# **Accessories**

## **Hub Opening Closure Plates**



Cat. No.	Description
BS051	Inside attachment for regular hub opening (i.e.: 1 in. to 2-1/2 in.)
BS054	Inside attachment for larger hub opening (i.e.: 3 in. to 4 in.)

#### **Insulated Neutral Kits**



Cat. No.	Description
IN1000BA, IN1000BE, IN1000PL	100 A Max.
IN2000BS, IN2000PL	200 A Max.

Specify socket upon ordering.

### **Insulated Neutral Kit**



Cat. No.	Description	
IN4000JS	400 A Max. (JS4)	

## **Ground Lug On Neutral Kit**

Cat. No.	Description
GN2000	200 A Max. for BQ2, BS2 Series

#### Micro-ID-Kit

Cat. No.	Description	Markers Kit Includes		
MINI-ID-KIT	Plastic case	Stainless steel markers of each numbers 0 thru 9 (dash + service)	10	
MICRO-ID-KIT	Blue metal carrying case	Stainless steel markers of each letters A thru D		
		Stainless steel markers of each numbers 0 thru 9	10	
		Words "SERVICE"		
		CM-BS100 Jumper Bar 200 A Max.	4	
		LS500 Meter Jaw Safetv Shroud	10	

Supplied with 4 Robertson head screws.

#### **Identification Markers**

Cat. No.	Description	
No. 0 through No. 9	Clipped to the upper lip of the enclosure; provides permanent customer identification.	
No. A through No. Z	Packed and sold in polyethylene bags of 10 identical markers except "SERVICE" which	
No. SERVICE	has 7 individual letters	

## Replacement + Block Assemblies



Cat. No.	Description	
ВАЗ-Х	Fits BA3 / BE1 Series	
BS2-X-UNI	Fits BQ2 / BS2 Series uni block	
MO2-X-UNI	Fits M02 Series uni block	
PL27-XEB	Fits PL27 Series uni block	

Add suffix "B" to cat. no. above if mounting bridge is required



# **Accessories**

#### **Fifth Jaw Assemblies**



Meter Socket	Standardcapacity 9 o' position	Full capacity 9 o' position Z105* Z205*		Full capacity 6 o' position		
Series	C205			CM-B106*	B306*†	
BA3	•	•				
BDC	•		•		•	
BE1	•	•		•		
BE2	•	•				
BEC	•	•				
BD2	•		•		•	
BQ2	•		•		•	
BS2 / BS2L	•		•		•	
BS4 / BSC4	•		•		•	
C01	•	•		•		
C02	•		•		•	
CO1 Multigang	•	•		•		

<sup>\*</sup> CSA not applicable † For mono blocks only

#### **Pole Mount Bracket Kit**

Cat. No.	Description	Conductor Range	Use w/Series	Option 1	Option 2
PMB200	Secures Microlectric meter socket to a wooden pole via Option 1 or 2	14-2 AWG	BA3, BE1, BQ2, BS, CL, CO1, CO2, CT, MO2, PL17, PL27, VT	Use a lag bolt through 5/8 in. center keyhole	Use the two side bracket mounting holes (0.320 in. dia.) to wrap around the pole

Suitable for any Microlectric meter socket with mounting holes 5 in. apart. Attach meter socket using one or two bracket(s). PMB200 kit comes complete with 2 brackets, 1 ground connector. Includes assembly hardware.

### **Pole Mounting Kit**

Cat. No.	Kit Includes	Qty.
PMBJS4	Support hangers	2
	1/2 in. x 4 in. lag bolt	1
	3/8 in. x 3 in. lag bolt	4
	5/16 in. x 1 in. carriage bolts, nuts and lock washers	4




Fifth Jaw Assemblies





## **Pole Line Hardware**

Cat. No.	Description	F Dia.	G Dia. (in.)	H Dia.	T Thick (in.)	Weight (100 pcs)		Ctd Dless
		(in.)		(in.)		lb.	kg	Std. Pkg.
RC729	Square washer	5/8	2	-	3/16	22	10.0	400
BC301L	Carriage bolt	3/8	1-1/2	1-1/2		11	5.0	
B0506	Oval eye bolt		6	3		122	55.4	
B0508		F/0	8	4	_	136	61.8	50
B0510		5/8	10	4		150	68.1	
B0512			12	4		168	76.3	





#### **Meter Adaptor Bracket**



Flexible Braid Kit



CIEFA-1/2 / CIEFA-4 CIEFSA-1/2 / CIEFSA-4

KO Conf	iguration
1/2 in.	3/4 in 1-1/4 in.

# **Accessories**

## **Meter Adaptor Bracket**

Cat. No.	Description
C03417M-1-FG	Adjustable Mounting Bracket for CO2 Series meters to adapt to Siemens, SD and Cutler Hammer breakers

#### **Flexible Braid Kit**

Cat. No.	Description
CO2FB-KIT	Connection wires adaptor kit for CO2 Series meter sockets for field installation. To be used with Cutler Hammer breakers

#### **Service Entrance Heads**

Cat. No.	Trade Size		
Service Entrance Heads (Cast Aluminum) Rigid Conduit			
CIEFA-1/2	1/2		
CIEFA-3/4	3/4		
CIEFA-1	1		
CIEFA-1 1/4	1-1/4		
CIEFA-1 1/2	1-1/2		
CIEFA-2	2		
CIEFA-2 1/2	2-1/2		
CIEFA-3	3		
CIEFA-3 1/2	3-1/2		
CIEFA-4	4		
Service Entrance Heads (Cast Aluminum) E.M.T.			
CIEFSA-1/2	1/2		
CIEFSA-3/4	3/4		
CIEFSA-1	1		
CIEFSA-1 1/4	1-1/4		
CIEFSA-1 1/2	1-1/2		

2-1/2

3-1/2

CIEFSA-2 1/2

CIEFSA-3 1/2

CIEFSA-4

Trade Size	<b>KO Dimensions</b>		
	Small	Large	Center
1/2	0.312	-	
3/4	0.375	0.400	_
1	0.438	0.500	
1-1/4		0.625	
1-1/2	0.610	0.750	0.400
2	0.750	1.000	0.525
2-1/2	0.875	1.300	1.000
3			
3-1/2	1.125	1.750	1.125
4			