

MO2M-V



Underground Only. 4 jaw. 4/0 for Manitoba.



General

Type:	BQ, BP, BS2, BS4M-V, MO2 Series
Notes for picture:	Picture represents the MO2 Series. Please refer to the specifications.
Application:	Manitoba
T&B UPC:	62487104169
T&B Status:	M
Voltage Rating:	600 V
Amperage Rating:	200 A

Dimension Information

Conductor Range:	Line: Single 1/2 in. studs to accommodate compression lugs 350 kcmil max. (supplied by utility), Load: 6 AWG-250 kcmil.
Height:	19-1/8 in.
Width:	12 in.