

**Rigid/IMC Conduit Fittings****T&B Catalog Number:**

1455

**UPC Number:**

78621001455

**Status:**

Active

**Description:**

1 1/2 in. Non-Metallic Knockout Plug, thermoplastic. For use with Rigid/IMC Conduit.

**Application**

To plug unused knockout openings in a box or enclosure.

**General**

Trade Size (inches)	1 1/2
---------------------	-------

Material	Thermoplastic
----------	---------------

**Dimension Information**

Dimension A (inches)	2.24
----------------------	------

Dimension B (inches)	0.57
----------------------	------

**Specifications**

3dmodel	Available on Website
---------	----------------------

**Packaging**

T&B Order Multiple	25
--------------------	----

T&B Inner Pack	25
----------------	----

Package in Units	100
------------------	-----

T&B Sold in UOM	Each
-----------------	------

T&B Weight Per UOM	4 lbs. per 100
--------------------	----------------

**Certifications**

RoHS Compliance	Yes
-----------------	-----

**Certifications**

File Nbr:

E 13938

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
www.tnb.com

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email:techsupport@tnb.com