Microlectric°


Meter Sockets

PL17 Series

Polyphase 100 A 600 V Max.


Product Specifications

- Conductor range: 6-1/0 AWG
- Aluminum tunnel type connectors for both load and line sides
- For overhead, underground and combination overhead/underground
- Supplied with screw type ring
- Weatherproof Type 3R enclosure
- · Primarily used in: All provinces





(PL17-INV)



COMBINATION AND UNDERGROUND BOTTOM



Cat. No.	Description	D	Dimensions (in.)			Weight Each	
		Н	W	D	lb.	kg	
7 JAW							
PL17-INV	Overhead, hub opening		8-9/16	5-7/16	12	5.4	
PL17-INV-HQ	Overhead, hub opening (Hydro-Quebec approved)						
PL17-INTV-HQ	Underground (Hydro-Quebec spec)						
PL17-INTCV	Combination overhead-underground	15-5/8					
PL17-INTCV-HQ	Combination overhead-underground (Hydro-Quebec approved)	10-0/0					
PL17-V	Overhead, hub opening						
PL17-TV	Underground						
PL17-TCV	Combination overhead-underground						
8 JAW							
PL17-8V	Overhead, hub opening	1E E/0	8-9/16	5-7/16	12	5.4	
PL17-8TCV	Combination overhead-underground	15-5/8					
FACTORY INSTALLE	D ACCESSORIES						
Include: -IN	Insulated neutral						

Trade Size

Knockout

1-11/16 in.

ł

Ø 1/2 in.

7/8 in.

1-1/16 in.



