



Liquidtight Flexible Cord & Cable Fittings

T&B Catalog Number:

2585

UPC Number:

78621002585

Status:

Active

Description:

2-1/2 in. straight malleable iron liquidtight strain relief cord connector, cord range-1.937-2.187.

Application

Suitable for use in hazardous locations where general purpose equipment is specifically permitted by NEC 501-4(b).

Meets Coast Guard CG293

General

Material Malleable Iron

Dimension Information

Hub Size (inches)	2 1/2
Dimension A (inches)	3 7/32
Dimension B (inches)	3 3/4
Dimension C (inches)	1 1/32
Cord Range (inches)	1.937-2.187
Throat Diameter (inches)	2

Specifications

3dmodel	Available on Website
Temperature Rating	105 C

Packaging

Package in Units	5
T&B Sold in UOM	Each
T&B Weight Per UOM	212 lbs. per 100

Application Support

Product Overview	Available on Website
Specifications	Available on Website
Portable Cord Selection Table	Available on Website

Notes

Suitable for use in hazardous locations where general purpose equipment is specifically permitted by NEC 501-4(b).

Certifications

RoHS Compliance	Yes
-----------------	-----

Certifications



File Nbr:
E 13938

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125

T&B Technical Support
MS 3B-50
8155 T&B Blvd.

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289

