



**Dual-Rated**  
**T&B Catalog Number:**

ADR21-21  
78378661009  
Active

**UPC Number:**  
**Status:**  
**Description:**

Type ADR-ALCUL Two-Conductor, One-Hole Mount for Conductor Range Max 2/0 Str., Min 14 AWG

**Features**

Easy Installation - no special tools required.

**General**

Style	ALCUL Two-Conductor, One-Hole Mount
Material	Aluminum
Plating	Tin-Plated
Conductor Range (AL or CU) Maximum	2/0 Str.
Conductor Range (AL or CU) Minimum	14 AWG

**Dimension Information**

Length (inches)	1 15/32
Width (inches)	1 1/4
Height (inches)	25/32
D (inches)	27/64
E (inches)	1/4
F (inches)	3/16
G (inches)	27/32
I (inches)	21/32

**Packaging**

T&B Inner Pack	12
Package in Units	120
T&B Sold in UOM	Each
T&B Weight Per UOM	7.19 lbs. per 100

**Notes**

UL 486B tested, AL9CU rated

**Certifications**

RoHS Compliance	Yes
-----------------	-----

**Certifications**



File Nbr:  
E9809

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
www.tnb.com

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email:techsupport@tnb.com

