



Dual-Rated
T&B Catalog Number:

ADR99-22D

UPC Number:

78378661050

Status:

Active

Description:

Type ADR-ALCUL Two-Conductor, Two-Hole Mount for Conductor Range Max 1000 kcmil, Min 500 kcmil

Features

Easy Installation - no special tools required.

General

Style	ALCUL Two-Conductor, Two-Hole Mount
Material	Aluminum
Plating	Tin-Plated
Conductor Range (AL or CU) Maximum	1000 kcmil
Conductor Range (AL or CU) Minimum	500 kcmil

Dimension Information

Length (inches)	6 3/16
Width (inches)	3 1/2
Height (inches)	1 7/8
D (inches)	5/8
E (inches)	1/2
F (inches)	9/16
G (inches)	3 7/16
I (inches)	1 13/16

Packaging

T&B Order Multiple	3
Package in Units	3
T&B Sold in UOM	Each
T&B Weight Per UOM	1.88 lbs. Each

Application Support

T&B Sales Drawings	wsd-000390
--------------------	------------

Notes

- NEMA spacing 1 3/4 inch centers.
- Connectors accomodating conductors 600 kcmil and larger have double rows of set screws (D suffix).
- UL 486B tested, AL9CU rated

Certifications

RoHS Compliance	No
-----------------	----

Certifications



File Nbr:
E9809

For further technical assistance, please contact us...

Memphis, TN 38125
www.tnb.com

8155 T&B Blvd.
Memphis, TN 38125

Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com