



**Rigid/IMC Conduit Fittings**

**T&B Catalog Number:**

374

**UPC Number:**

78621000374

**Status:**

Active

**Description:**

1 1/2 in. Hub Connector, Malleable Iron-Electro Zinc Plated, Nylon Insulated. For use with Rigid/IMC Conduit.

**Features**

Rugged steel/malleable iron construction
Tapered internal threads for water-tight/dust-tight union
Threads relieved to prevent bottoming of conduit, ensuring sound assembly
Recessed sealing ring at box end; sealing ring captivated
Hardened steel/malleable iron/copper-free aluminum locknuts designed to provide high quality ground continuity; extended reach of locknut permits clamping on thin boxes and enclosures
Insulated throat, insulates conductors, prevents abrasion and thinning of conductor insulation, reduces wire pull effort

**Application**

To connect threaded metal conduit (ferrous rigid/non-ferrous rigid/PVC coated/or intermediate metal) to a threadless opening in a box or enclosure in outdoor or indoor location exposed to continuous or intermittent moisture.
To positively bond conduit to box or enclosure.
Suitable for hazardous locations use in Class I, Division 2; Class II, Division 1&2; Class III, Division 1 & 2 per NEC 501-4(b); 502-4 (a) and 503-3 (a).
Suitable for hazardous locations use in Class II, Groups E, F, G & Class III locations per CEC 18-202; 18-252; 18-302; 18-352.
When used with neoprene O-ring, provides water-tight threaded hub on enclosures
UL Listed 105 degree C

**General**

Trade Size (inches)	1-1/2
Material	Malleable Iron
Finish	Electro Zinc Plated

**Dimension Information**

Dimension A (inches)	3 3/32
Dimension B (inches)	1 5/8
Dimension C (inches)	1

**Specifications**

3dmodel	Available on Website
---------	----------------------

**Packaging**

T&B Inner Pack	2
Package in Units	10

T&B Sold in UOM	Each
T&B Weight Per UOM	77.5 lbs. per 100

## Application Support

Spacing Chart	Available on Website
---------------	----------------------

## Notes

Available with DURA-PLATE Finish

## Certifications

RoHS Compliance	Yes
-----------------	-----

## Certifications



File Nbr:

E 23018

### For further technical assistance, please contact us...

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
www.tnb.com

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email:techsupport@tnb.com