



Split-Bolt
T&B Catalog Number:

6HPS
 78378620042
 Active

UPC Number:
Status:
Description:

Type HPS Plated Split-Bolt Connector with Spacer made of Copper Alloy for Use on Copper, Aluminum, ACSR Conductors. Conductor Range for Equal Main and Tap 6 Sol.-12 Sol.

Features

Bolt and pressure bar of copper alloy, completely tin plated for corrosion resistance. Contoured spacer of electrolytic copper.

Application

Splicing, tapping or terminating conductors in power and grounding electrical connection.

General

Style	Type HPS
Wire Type	Copper, Aluminum, ACSR
Material	Copper Alloy
Plating	Electro Tin-Plated
Color	Metallic
Conductor Range for Equal Main and Tap 6 Sol.-12 Sol.	
Conductor Range Min. Tap with one Max. 12 Sol.	
Main	
Conductor Range For Equal Main and Tap ACSR	8

Dimension Information

A (inches)	15/32
B (inches)	0.170
C (inches)	21/32
D (inches)	1 1/8

Packaging

T&B Inner Pack	100
Package in Units	600
T&B Sold in UOM	Each
T&B Weight Per UOM	6 lbs. per 100

Application Support

T&B Sales Drawings	wsd-000072
--------------------	------------

Notes

Most connectors are UL and CSA Certified for copper conductor only.
 Blackburn Contax recommended when used on aluminum conductor.

Certifications

RoHS Compliance	Yes
-----------------	-----

Certifications



File Nbr:
E9809

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com