



Cast PAA

Parallel Groove Connector

T&B Catalog Number:

PAA109

UPC Number:

78378633011

Status:

Active

Description:

Aluminum Type PAA - One and Two Bolt Aluminum Parallel Groove Clamp for Wire Range Main: 336.4-1/0, 1/0-6 AR ASCR 400-1/0 Str., 1/0-6 AR AL/CU, Tap: 1/0-8 ASCR 1/0 Str.-8 Sol. ALCU

Features

Clamps are high-strength, heat treated cast aluminum alloy. Galvanized-steel carriage bolt, nut and lockwasher standard. Order prefilled with oxide inhibitor for use on copper to aluminum.

General

Style	Type PAA - One and Two Bolt Aluminum Clamp
Material	Aluminum
Conductor Range (AL or CU) Main	400-1/0 Str., 1/0-6 AR
Conductor Range (AL or CU) Tap	1/0 Str.-8 Sol.
Conductor Range ASCR Main	336.4-1/0, 1/0-6 AR
Conductor Range ASCR Tap	1/0-8

Dimension Information

Bolt Size (inches)	3/8
F (inches)	9/16
H (inches)	2 15/32
L (inches)	2
W (inches)	1 3/4
Conductor Diameter Main Max.	0.741
Conductor Diameter Main Min.	0.368
Conductor Diameter Tap Max.	0.398
Conductor Diameter Tap Min.	0.128

Packaging

Package in Units	25
T&B Sold in UOM	Each
T&B Weight Per UOM	25.72 lbs. per 100

Notes

To order with hex head bolts, add suffix -3.

One-bolt clamp.

AR = Over armor rod.

Certifications

RoHS Compliance	Yes
-----------------	-----

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com