



H-Tap Connectors T&B Catalog Number:

UPC Number:
Status:
Description:

WR399
78378610010
Active

Aluminum Wide Range H-Type Compression Connector Main: 4/0 - 3/0 ACSR, 4/0 - 3/0 Str. Tap: 2/0 - 1 ACSR, 2/0 - 1/0 Str. 3/0 - 2/0 Sol.

Features

Made of 1350 Aluminum alloy to provide high strength and conductivity. Prefilled with oxide inhibitor held captive in the rib/connection area.

Enables excellent connector contact without distorting the conductor's shape.

Fold-in tabs provide positive tab interlock as tool closes.

RUS accepted and complies with ANSI C119.4

General

Style	Type WR - Supplemental O and D Die Connectors
Material	Aluminum
Standard Conductor Main - ACSR	4/0, 3/0
Standard Conductor Main - Stranded	4/0, 3/0
Standard Conductor Tap - ACSR	2/0, 1/0, 1
Standard Conductor Tap - Stranded	2/0, 1/0
Standard Conductor Tap - Solid	3/0, 2/0
Compact Conductor Main - ACSR	266 18/1, 4/0, 3/0
Compact Conductor Main - Stranded	266, 250, 4/0
Compact Conductor Tap - ACSR	2/0, 1/0
Compact Conductor Tap - Stranded	3/0, 2/0, 1/0

Dimension Information

Length (inches)	2 3/16"
Conductor Diameter Main Max.	0.563
Conductor Diameter Main Min.	0.461
Conductor Diameter Tap Max.	0.447
Conductor Diameter Tap Min.	0.338

Tooling

Application Tools	JB12A, JB12B, 12A, Y-35
Connector Die	D
No. Indents Mechanical Tool	6
No. Indents Hydraulic Tool	2

Packaging

T&B Inner Pack	25
Package in Units	250
T&B Sold in UOM	Each
T&B Weight Per UOM	17.19 lbs. per 100

Certifications

RoHS Compliance	Yes
-----------------	-----

For further technical assistance, please contact us...

Memphis, TN 38125
www.tnb.com

8155 T&B Blvd.
Memphis, TN 38125

Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com