



Dual-Rated T&B Catalog Number:

UPC Number:
Status:
Description:

ADR25-32
78378661013
Active

Type ADR-ALCUL Three-Conductor, Two-Hole Mount for Conductor Range Max 250 kcmil, Min 6 Str.

Features

Easy Installation - no special tools required.

General

Style	ALCUL Three-Conductor, Two-Hole Mount
Material	Aluminum
Plating	Tin-Plated
Conductor Range (AL or CU) Maximum	250 kcmil
Conductor Range (AL or CU) Minimum	6 Str.

Dimension Information

Length (inches)	4 3/16
Width (inches)	2 13/16
Height (inches)	1 1/4
D (inches)	5/8
E (inches)	1/2
F (inches)	1/4
G (inches)	3 1/16
I (inches)	31/32

Packaging

T&B Inner Pack	6
Package in Units	60
T&B Sold in UOM	Each
T&B Weight Per UOM	55.31 lbs. per 100

Notes

NEMA spacing 1 3/4 inch centers.

Connectors accommodating conductors 600 kcmil and larger have double rows of set screws (D suffix).

UL 486B tested, AL9CU rated

Certifications

RoHS Compliance	Yes
-----------------	-----

Certifications



File Nbr:
E9809

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com