



**Liquidtight Flexible Cord & Cable Fittings**

**T&B Catalog Number:**

2691

**UPC Number:**

78621002691

**Status:**

Active

**Description:**

3/8 in. Black Beauty nylon straight liquidtight cord connector, cord range-.125 -.275.

**Features**

Hand tightens, no tools needed for assembly.

Segmented chuck provides high mechanical pullout performance, will not cut or damage cord jacket.

**Application**

To connect flexible cord to a box or enclosure and provide adequate strain relief.

Suitable for use in hazardous locations where general purpose equipment is specifically permitted by NEC. Class I, Div 2; Class II, Div 1 & 2; Class III, Div 1 & 2; NEC 501-4(b), 502-4(a)(b), 503-3(a)(b)

Meets Coast Guard CG293

**General**

Material Nylon

**Dimension Information**

Hub Size (inches) 1/2  
 Dimension A (inches) 3.0  
 Dimension B (inches) 1.57  
 Dimension C (inches) 0.60  
 Cord Range (inches) .560-.690  
 Throat Diameter (inches) 0.54

**Specifications**

3dmodel Available on Website  
 Temperature Rating 34 C - 105 C

**Packaging**

T&B Inner Pack 10  
 Package in Units 100  
 T&B Sold in UOM Each  
 T&B Weight Per UOM 12.31 lbs. per 100

**Application Support**

T&B Instruction Sheets ta01320-tb2  
 Product Overview Available on Website  
 Portable Cord Selection Table Available on Website

**Notes**

Remove sufficient outer covering of cable to permit conductors to pass thru connector body.

**Certifications**

RoHS Compliance Yes

## Certifications



File Nbr:  
E 13938

### For further technical assistance, please contact us...

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)