



Splice Connector

T&B Catalog Number:

RBB217-200

UPC Number:

78621081955

Status:

Active

Description:

Expanded Insulated Vinyl Butt Splice Connector For Wire Range 16-14
Length 1.13 Diameter .26, Blue

WEB_USE

US Cutsheet PDF Catalog Link

<http://www-public.tnb.com/contractor/docs/stakon.pdf>

Features

In butt splices, the wires are butted together and crimped at each end of the splice. These splices are color-coded according to wire size.



General

Insulation Type	Expanded Insulated Vinyl
Terminal Series	RBB
Material	Copper
Finish	Electro -Tin Plated
Color	Blue
Wire Range	16-14

Dimension Information

Maximum Insulation (inches)	.200
Stock Thickness	.03
A (inches)	1.13
B (inches)	.26

Specifications

Temperature Rating	105°C
Voltage Rating	600V
Flammability Rating	UL 94 V-0

Tooling

Tool Charts	Available on Website
Application Tools	WT145C, WT2000, WT112M, ERG4001, ERG4003
Recommended Tool	ERG4001

Packaging

T&B Order Multiple	1000
T&B Inner Pack	1000
Package in Units	10000
Package Type	Bulk
T&B Sold in UOM	Each
T&B Weight Per UOM	0.36 lbs. per 100
Alternate Package Qty	2RB14X

Application Support

Overview	Available on Website
Wire Guide Tables	Available on Website

Certifications

RoHS Compliance	Yes
-----------------	-----

Certifications



File Nbr:
E9809

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com