



Liquidtight Flexible Cord & Cable Fittings

T&B Catalog Number:

2922AL

UPC Number:

78621079715

Status:

Active

Description:

1/2 in. straight aluminum Ranger liquidtight cord connector, cord range .500-.750

Features

- Extended range with superior strain relief.
- Reduced overall size, fits into tighter spaces.
- Gland nut designed to restrict cable bending.

Application

- Provide a means for passing a cord cable into an enclosure through a bulkhead
- Suitable for Ordinary, Wet or Dry locations.
- Suitable for use in hazardous locations where general purpose equipment is specifically permitted by NEC 501-4(b).

General

Material	Aluminum
Cord and Cable Types	S, SO, SV, ST, STD, SJ, SJO, SJT, SJTO, SVD

Dimension Information

Hub Size (inches)	1/2
Dimension A (inches)	1 5/16
Dimension B (inches)	1 3/4
Dimension C (inches)	5/8
Cord Range (inches)	.500-.750
Throat Diameter (inches)	9/16

Specifications

3dmodel	Available on Website
---------	----------------------

Packaging

T&B Inner Pack	25
Package in Units	100
T&B Sold in UOM	Each
T&B Weight Per UOM	9.94 lbs. per 100

Application Support

T&B Sales Drawings	wsd-000077
Product Overview	Available on Website
Specifications	Available on Website
Portable Cord Selection Table	Available on Website

Notes

Suitable for use in hazardous locations where general purpose equipment is specifically permitted by NEC 501-4(b).

Certifications

RoHS Compliance	Yes
-----------------	-----

Certifications



File Nbr:
E 13938

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com