



## Standard Barrel Copper Lug T&B Catalog Number:

54110

**UPC Number:** 78621054110

**Status:** Active

### Description:

Copper One-Hole Lug - Straight Standard Barrel - max 35KV, 2/0 AWG Wire, 3/8" Bolt Size, Tin Plated with Inspection Hole, Black 45

### General

Material	Copper
Finish	Tin Plated
Wire Size	2/0 AWG
Number of Studs	1
Stud Size	3/8
Tongue Angle	Straight
Barrel Length	Standard
Barrel Shape	Standard
Tongue Width	Standard
Peep Hole	Y
Marking	Standard
Hole Shape	Round
Die Color	Black
Die Code	45

### Dimension Information

A (inches)	1.93
B (inches)	0.93
C (inches)	0.83
D (inches)	0.13
E (inches)	0.57
F (inches)	3/8

### Tooling

Connector & Tooling Chart	Available on Website
---------------------------	----------------------

### Packaging

T&B Order Multiple	10
T&B Inner Pack	10
Package in Units	100
T&B Sold in UOM	Each
T&B Weight Per UOM	6.88 lbs. per 100

### Application Support

T&B Instruction Sheets	ta00675-tb2
Product Overview	Available on Website

### Notes

Dimensions given for reference only. Dimensions may vary up to .030.

### Certifications

RoHS Compliance	Yes
-----------------	-----

**For further technical assistance, please contact us...**

Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

8155 T&B Blvd.  
Memphis, TN 38125

Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)