Thomas&Betts



Splice Connector T&B Catalog Number:

UPC Number: Status: **Description:**

54504 78621054504 Active

Copper Two-Way Splice - Short Barrel for 8 AWG, 37/24, 8 Weld, Die Code 21 Red Features

> Two-way connectors provide high pullout values, are easy to insulate and provide a low-resistance connection of high quality and low installed cost.

	3 1
General	
Style	Two-Way Standard Barrel Splice
Material	Copper
Finish	Tin-Plated
Wire Size	#8 AWG
Wire Size Flex	37/24 = 14.9 kcmil, #8 Weld
Die Color	Red
Die Code	21
Dimension Information	
A (inches)	1.00
E (inches)	.27
Specifications	
Voltage Rating	600V
Packaging	
T&B Inner Pack	50
Package in Units	500
T&B Sold in UOM	Each
T&B Weight Per UOM	1.12 lbs. per 100
Application Support	• •
T&B Instruction Sheets	ta00676-tb2
Certifications	
RoHS Compliance	Yes
Certifications	
~ ^	
(UL) (SP -	





File Nbr:

Y

For further technical assistance, please contact us...

T&B Technical Support MS 3B-50 8155 T&B Blvd. Memphis, TN 38125

Hours: 7AM - 6PM CDT Monday-Friday Phone: (888) 862-3289 Fax: (901) 252-1321 Email:techsupport@tnb.com

Thomas & Betts - USA 8155 T&B Blvd. Memphis, TN 38125 www.tnb.com