



Disconnects

T&B Catalog Number:

RA257

UPC Number:

78621081703

Status:

Active

Description:

Insulated Vinyl Female - 250 Series Disconnects For Wire Range 22-18
Length 0.96, Tab Size .250 x .032 , Red

WEB_USE

US Cutsheet PDF Catalog Link

<http://www-public.tnb.com/contractor/docs/stakon.pdf>

Features

Unique construction of the female disconnect offers long-term dependability. Brazed seam serrated barrel provides maximum tensile strength.

General

Disconnect Type	Female - 250 Series
Insulation Type	Insulated Vinyl
Terminal Series	RA
Material	Brass
Finish	Electro -Tin Plated
Color	Red
Wire Range	22-18
Tab Size	.250 x .032

Dimension Information

Maximum Insulation (inches)	.150
Stock Thickness	.03
A (inches)	.96
B (inches)	.29

Specifications

Temperature Rating	105°C
Voltage Rating	600V
Flammability Rating	UL 94 V-0

Tooling

Tool Charts	Available on Website
Application Tools	WT145C, WT2000, WT112M, ERG4001, ERG4003
Recommended Tool	ERG4001

Packaging

T&B Order Multiple	1000
T&B Inner Pack	1000
Package in Units	10000
Package Type	Bulk
T&B Sold in UOM	Each
T&B Weight Per UOM	0.28 lbs. per 100
Alternate Package Qty	18RA250F

Application Support

Overview	Available on Website
Wire Guide Tables	Available on Website

Notes

Bulk catalog numbers can be put on Mylar Tape for reel-fed applications (i.e. 12050 tool and application dies). Please add the suffix M for Mylar tape.

Certifications

RoHS Compliance Yes

Certifications



File Nbr:
E66716

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com