

DH017C12-C

Hazlux®

Hazlux 3 standard housing fixture metal halide lamp. 175 W.



General

Type:	Hazlux 3 Standard Housing
Application:	For hazardous location
T&B UPC:	78621030383
T&B Status:	M
Series:	Hazlux 3 Fixture
Housing:	Standard Housing
Special Features:	Canadian Market
Lamp Type:	Metal Halide
Lamp Wattage:	175 W
Voltage Rating:	120 V, 60 Hz
Ballast Circuit:	Constant Wattage Autotransformer (CWA)
Starter Circuit:	Standard Fixture (without options)