



**Liquidtight Flexible Cord & Cable Fittings**

**T&B Catalog Number:**

2518

**UPC Number:**

78621002518

**Status:**

Active

**Description:**

3/8 in. straight steel liquidtight strain relief cord connector, cord range-.060-.150.

**Application**

Suitable for use in hazardous locations where general purpose equipment is specifically permitted by NEC 501-4(b).

Meets Coast Guard CG293

**General**

Material Steel

**Dimension Information**

Hub Size (inches) 3/8  
 Dimension A (inches) 31/32  
 Dimension B (inches) 1 1/2  
 Dimension C (inches) 15/32  
 Cord Range (inches) .060-.150  
 Throat Diameter (inches) 29/64

**Specifications**

3dmodel Available on Website  
 Temperature Rating 105 C

**Packaging**

T&B Inner Pack 25  
 Package in Units 100  
 T&B Sold in UOM Each  
 T&B Weight Per UOM 10.63 lbs. per 100

**Application Support**

Product Overview Available on Website  
 Specifications Available on Website  
 Portable Cord Selection Table Available on Website

**Notes**

Suitable for use in hazardous locations where general purpose equipment is specifically permitted by NEC 501-4(b).

**Certifications**

RoHS Compliance Yes

**Certifications**



File Nbr:  
 E 13938

**For further technical assistance, please contact us...**

8155 T&B Blvd.  
Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)