



## Armored Cable/Flexible Metal Conduit Fittings

### T&B Catalog Number:

326-TB

### UPC Number:

78621000326

### Status:

Active

### Description:

1 in. Tite-Bite 90 Degree Connector, Malleable Iron-Electro Zinc Plated.

### Features

The angle clip gives secure mechanical grip that tightens under tension or vibration.

Throat is long enough to install in cast housing knockouts.

### Application

For use with Armored Cable and Flexible Metal Conduit.

To connect and effectively bond armored cable or flexible metal conduit to a box or an enclosure.

### General

Trade Size (inches)

1

Material

Malleable Iron

Finish

Electro Zinc Plated

### Dimension Information

Dimension A (inches)

2 21/32

Dimension B (inches)

2 1/8

Dimension C (inches)

1

Knockout Size (inches)

1

Cable Opening-Minimum (inches)

1.25

Cable Opening-Maximum (inches)

1.468

### Specifications

3dmodel

Available on Website

### Packaging

T&B Inner Pack

5

Package in Units

25

T&B Sold in UOM

Each

T&B Weight Per UOM

52.8 lbs. per 100

### Certifications

RoHS Compliance

No

### Certifications



File Nbr:

E 23018

For further technical assistance, please contact us...

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
www.tnb.com

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: techsupport@tnb.com