



## E-Z-Ground Compression Grounding

### T&B Catalog Number:

**UPC Number:**

53065

**Status:**

78621053065

**Description:**

Active

E-Z-Ground Ground Grid Copper Compression Connector for Cable Range 4/0 - 250 kcmil, Tap 4/0 - 250 kcmil, Ground Rod 1/2, 5/8

### Features

E-Z-Ground® connectors are designed for direct burial and offer a safe, efficient alternative to exothermic welding products.

### General

Style	Ground Grid
Material	Copper
Wire Range	4/0 - 250 kcmil
Copperclad Wire Size	7/16 (19 #9) or (7#5)
Application / Main	4/0 - 250 kcmil
Application / Tap	4/0 - 250 kcmil
Ground Rod	1/2, 5/8
Die Code (Cable to Cable)	87H
Die Code (Rod to Cable)	87H

### Dimension Information

L1 (inches)	4 7/16
L2 (inches)	4.3125

### Tooling

Die Selection Charts	Available on Website
Application Tools	TBM14M, 13100A, TBM15I

### Packaging

T&B Inner Pack	2
Package in Units	10
T&B Sold in UOM	Each
T&B Weight Per UOM	130 lbs. per 100

### Application Support

Overview	Available on Website
----------	----------------------

### Notes

Does not meet IEEE 837 Requirements.

Cat No. 15500 adapter as required for all 15500 Series dies, not for 15600 dies. Hydraulic tools only.

Ground rods 4/0-250 wire barrels suitable for 1/2" smf 5/8" rod. 500 kdmil wire barrels suitable for 1" rods. 300-500 kcmil wire barrels suitable for 5/8" rods.

### Certifications

RoHS Compliance	Yes
-----------------	-----

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289

