

## Rigid/IMC Conduit Fittings T&B Catalog Number:

372

**UPC Number:** 78621000372

**Status:** Active

**Description:** 

1 in. Hub Connector, Steel-Electro Zinc Plated, Nylon Insulated. For use with Rigid/IMC Conduit.

with Rigid/livic Conduit.	
Features	
	Rugged steel/malleable iron construction
	Tapered internal threads for water-tight/dust-tight
	union
	Threads relieved to prevent bottoming of conduit,
	ensuring sound assembly
	Recessed sealing ring at box end; sealing ring cap-
	tivated
	Hardened steel/malleable iron/copper-free alu-
	minum locknuts designed to provide high quality
	ground continuity; extended reach of locknut per-
	mits clamping on thin boxes and enclosures
	Insulated throat, insulates conductors, prevents
	abrasion and thinning of conductor insulation, re-
	duces wire pull effort
Application	adood fino pain onor.
•••	
	To connect threaded metal conduit (ferrous rigid/
	non-ferrous rigid/PVC coated/or intermediate metal)
	to a threadless opening in a box or enclosure in out-
	door or indoor location exposed to continuous or in-
	termittent moisture.
	To positively bond conduit to box or enclosure.
	Suitable for hazardous locations use in Class I, Di-
	vision 2; Class II, Division 1&2; Class III, Division 1
	& 2 per NEC 501-4(b); 502-4 (a) and 503-3 (a).
	Suitable for hazardous locations use in Class II,
	Groups E, F, G & Class III locations per CEC 18-
	202; 18-252; 18-302; 18-352.
	When used with neoprene O-ring, provides water-
	tight threaded hub on enclosures
	UL Listed 105 degree C
General	
Trade Size (inches)	1
Material	Steel
Finish	Electro Zinc Plated
<b>Dimension Information</b>	
D:	0.0/00
Dimension A (inches)	2 3/32
Dimension B (inches)	1 3/8
Dimension C (inches)	7/8
Specifications	
3dmodel	Available on Website
Packaging	
T&B Inner Pack	5
	5
Package in Units	25



T&B Sold in UOM
T&B Weight Per UOM
39.2 lbs. per 100

Application Support

Spacing Chart
Available on Website

Notes

Availabe with DURA-PLATE Finish

Certifications

RoHS Compliance
Yes

Certifications



File Nbr: E 23018

## For further technical assistance, please contact us...

T&B Technical Support MS 3B-50 8155 T&B Blvd. Memphis, TN 38125 Hours: 7AM - 6PM CDT Monday-Friday Phone: (888) 862-3289 Fax: (901) 252-1321 Email:techsupport@tnb.com

Thomas & Betts - USA 8155 T&B Blvd. Memphis, TN 38125 www.tnb.com