



## Liquidtight Flexible Cord & Cable Fittings

**T&B Catalog Number:**

2545

**UPC Number:**

78621002545

**Status:**

Active

**Description:**

1 in. straight die cast zinc liquidtight strain relief cord connector, cord range-.625-.750.

### Application

Suitable for use in hazardous locations where general purpose equipment is specifically permitted by NEC 501-4(b).

Meets Coast Guard CG293

### General

Material Die Cast Zinc

### Dimension Information

Hub Size (inches)	1
Dimension A (inches)	1 3/8
Dimension B (inches)	1 23/32
Dimension C (inches)	25/32
Cord Range (inches)	.625-.750
Throat Diameter (inches)	49/64

### Specifications

3dmodel	Available on Website
Temperature Rating	105 C

### Packaging

T&B Inner Pack	10
Package in Units	100
T&B Sold in UOM	Each
T&B Weight Per UOM	24.19 lbs. per 100

### Application Support

Product Overview	Available on Website
Specifications	Available on Website
Portable Cord Selection Table	Available on Website

### Notes

Suitable for use in hazardous locations where general purpose equipment is specifically permitted by NEC 501-4(b).

### Certifications

RoHS Compliance Yes

### Certifications



File Nbr:  
E 13938

**For further technical assistance, please contact us...**

8155 T&B Blvd.  
Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)