



Splice Connector
T&B Catalog Number:

54818

UPC Number:

78621054818

Status:

Active

Description:

Copper Two-Way Splice - Long Barrel for 500 kcmil, 925/24 Die Code 87
 Brown

Features

Two-way connectors provide high pullout values, are easy to insulate and provide a low-resistance connection of high quality and low installed cost.

General

Style	Two-Way Long Barrel Splice
Material	Copper
Finish	Tin-Plated
Wire Size	500 kcmil
Wire Size Flex	925/24 = 373 kcmil
Die Color	Brown
Die Code	87

Dimension Information

A (inches)	4.75
E (inches)	1.11

Specifications

Voltage Rating	600V
----------------	------

Packaging

T&B Order Multiple	6
T&B Inner Pack	6
Package in Units	60
T&B Sold in UOM	Each
T&B Weight Per UOM	55.69 lbs. per 100

Application Support

T&B Instruction Sheets	ta00674-tb2
------------------------	-------------

Notes

UL Listed for direct burial applications.

Certifications

RoHS Compliance	Yes
-----------------	-----

Certifications



File Nbr:

Y

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
 www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email:techsupport@tnb.com

