



Disconnects
T&B Catalog Number:

RBD14-187A

UPC Number:

78621076989

Status:

Active

Description:

Fully Insulated Nylon Female - 187 Series Flag Disconnects For Wire Range 16-14 Length 0.74, Tab Size .187 x .032 , Blue

WEB_USE

US Cutsheet PDF Catalog Link

<http://www-public.tnb.com/contractor/docs/stakon.pdf>

Features

Quick, reliable method of connection to terminal blocks and boards without the use of tools. Unique construction of the female disconnect offers long-term dependability.

General

Disconnect Type	Female - 187 Series Flag
Insulation Type	Fully Insulated Nylon
Terminal Series	RBD
Material	Brass
Finish	Electro -Tin Plated
Color	Blue
Wire Range	16-14
Tab Size	.187 x .032

Dimension Information

Maximum Insulation (inches)	.170
Stock Thickness	.03
A (inches)	.74
B (inches)	.61

Specifications

Temperature Rating	105°C
Voltage Rating	600V
Flammability Rating	UL 94 V-2

Tooling

Tool Charts	Available on Website
Application Tools	WT145C, WT2000, WT112M, ERG4001, ERG4003
Recommended Tool	ERG4001

Packaging

T&B Order Multiple	50
T&B Inner Pack	50
Package in Units	250
Package Type	Bulk
T&B Sold in UOM	Each
T&B Weight Per UOM	0.42 lbs. per 100
Alternate Package Qty	RBD1877F

Application Support

Overview	Available on Website
Wire Guide Tables	Available on Website

Certifications

RoHS Compliance Yes

Certifications



File Nbr:
E66716

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com