



Splice Connector T&B Catalog Number:

54018
78621054018
Active

UPC Number:
Status:
Description:

Copper Two-Way Splice - Long Barrel for 500 kcmil, Die Set 15CA87R
Brown

Features

Two-way connectors provide high pullout values, are easy to insulate and provide a low-resistance connection of high quality and low installed cost.

General

Style	Two-Way Long Barrel Splice
Material	Copper
Finish	Tin-Plated
Wire Size	500 kcmil
Strip Length (inches)	2 5/8
Die Color	Brown
Die Set	15CA87R



Dimension Information

Strip Length (inches)	2 5/8
A (inches)	4.13
E (inches)	1.06

Specifications

Voltage Rating	600V
----------------	------

Tooling

Application Tools	13100A, TBM15I, TBM14M
-------------------	------------------------

Packaging

T&B Order Multiple	6
T&B Inner Pack	6
Package in Units	60
T&B Sold in UOM	Each
T&B Weight Per UOM	47.69 lbs. per 100

Notes

Cat. No. 15500-TB Die Adapter required for TBM15I Tool.

Certifications

RoHS Compliance	Yes
-----------------	-----

Certifications



File Nbr:

Y

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125

T&B Technical Support
MS 3B-50
8155 T&B Blvd.

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289

