



## Fork Terminal T&B Catalog Number:

RB657

## UPC Number:

78621081834

## Status:

Active

## Description:

Insulated Vinyl Fork Terminal For Wire Range 18-14 Stud Size #8, Blue  
**WEB\_USE**

US Cutsheet PDF Catalog Link

<http://www-public.tnb.com/contractor/docs/stakon.pdf>

## Features

These fork terminals have extra-long PVC insulation sleeve for protection and stress relief at wire's flex point. Braze seam barrel is serrated for high pull-out value. Insulation is color-coded.

## General

Insulation Type	Insulated Vinyl
Terminal Series	RB
Material	Copper
Finish	Electro -Tin Plated
Color	Blue
Wire Range	18-14
Stud Size	#8

## Dimension Information

Maximum Insulation (inches)	.170
Stock Thickness	.03
A (inches)	.97
B (inches)	.31
C (inches)	.27
M (inches)	.81

## Specifications

Temperature Rating	105°C
Voltage Rating	600V
Flammability Rating	UL 94 V-0

## Tooling

Tool Charts	Available on Website
Application Tools	WT145C, WT2000, WT112M, ERG4001, ERG4003
Recommended Tool	ERG4001

## Packaging

T&B Order Multiple	1000
T&B Inner Pack	1000
Package in Units	10000
Package Type	Bulk
T&B Sold in UOM	Each
T&B Weight Per UOM	0.25 lbs. per 100
Alternate Package Qty	14RB-8F

## Application Support

Overview	Available on Website
Wire Guide Tables	Available on Website

## Notes

Most terminals can be put on Mylar Tape for reel fed applications by adding the suffix M to the bulk catalog numbers.

## Certifications

RoHS Compliance Yes

## Certifications



File Nbr:  
E9809

### For further technical assistance, please contact us...

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
www.tnb.com

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email:techsupport@tnb.com