



Liquidtight Flexible Cord & Cable Fittings

T&B Catalog Number:

2704

UPC Number:

78621002704

Status:

Active

Description:

1-1/4 in. Black Beauty nylon straight liquidtight cord connector, cord range-1.270 -1.470.

Features

Hand tightens, no tools needed for assembly.

Segmented chuck provides high mechanical pullout performance, will not cut or damage cord jacket.

Application

To connect flexible cord to a box or enclosure and provide adequate strain relief.

Suitable for use in hazardous locations where general purpose equipment is specifically permitted by NEC. Class I, Div 2; Class II, Div 1 & 2; Class III, Div 1 & 2; NEC 501-4(b), 502-4(a)(b), 503-3(a)(b)

Meets Coast Guard CG293

General

Material Nylon

Dimension Information

Hub Size (inches) 1 1/4
 Dimension A (inches) 4.0
 Dimension B (inches) 2.58
 Dimension C (inches) 0.80
 Cord Range (inches) 1.270-1.470
 Throat Diameter (inches) 1.25

Specifications

3dmodel Available on Website
 Temperature Rating 34 C - 105 C

Packaging

T&B Inner Pack 2
 Package in Units 10
 T&B Sold in UOM Each
 T&B Weight Per UOM 27.5 lbs. per 100

Application Support

T&B Instruction Sheets ta01320-tb2
 Product Overview Available on Website
 Portable Cord Selection Table Available on Website

Notes

Remove sufficient outer covering of cable to permit conductors to pass thru connector body.

Certifications

RoHS Compliance Yes

Certifications



File Nbr:
E 13938

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com