



## Wire Joints T&B Catalog Number:

RB44  
78621080430  
Active

## UPC Number: Status: Description:

Insulated Nylon Wire Joints for Minimum Wire Range 2 (#18) to Maximum Wire Range 2 (#16), White

### WEB\_USE

US Cutsheet PDF Catalog Link <http://www-public.tnb.com/contractor/docs/stakon.pdf>

### Standards

UL, CSA

### Application

Provides terminating point for a group of wires running in one direction.

### General

Insulation Type	Insulated Nylon
Terminal Series	RB
Color	White
Wire Range	2 (#18) - 2 (#16)

### Dimension Information

Stock Thickness	.03
A (inches)	.31
B (inches)	.78

### Tooling

Tool Charts	Available on Website
Application Tools	WT2000
Recommended Tool	WT2000

### Packaging

T&B Order Multiple	100
T&B Inner Pack	100
Package in Units	500
Package Type	Standard
T&B Sold in UOM	Each
T&B Weight Per UOM	0.22 lbs. per 100

### Application Support

Overview	Available on Website
Wire Guide Tables	Available on Website

### Certifications

RoHS Compliance	Yes
-----------------	-----

### Certifications



File Nbr:  
E9809

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)