



Splice Connector
T&B Catalog Number:

54811
 78621054811
 Active

UPC Number:
Status:
Description:

Copper Two-Way Splice - Long Barrel for 3/0 AWG, 325/24 Die Code 50 Orange

Features

Two-way connectors provide high pullout values, are easy to insulate and provide a low-resistance connection of high quality and low installed cost.

General

Style	Two-Way Long Barrel Splice
Material	Copper
Finish	Tin-Plated
Wire Size	3/0 AWG
Wire Size Flex	325/24 = 131 kcmil
Die Color	Orange
Die Code	50

Dimension Information

A (inches)	2.25
E (inches)	0.65

Specifications

Voltage Rating	600V
----------------	------

Packaging

T&B Inner Pack	10
Package in Units	100
T&B Sold in UOM	Each
T&B Weight Per UOM	9.05 lbs. per 100

Application Support

T&B Instruction Sheets	ta00674-tb2
------------------------	-------------

Certifications

RoHS Compliance	Yes
-----------------	-----

Certifications



File Nbr:
 Y

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
 www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email:techsupport@tnb.com

