



Disconnects T&B Catalog Number:

BD14-183
78621081447
Active

UPC Number: Status: Description:

Non-Insulated Female - 187 Series Disconnects For Wire Range 16-14
Length 0.64, Tab Size .187 x .032 , Metallic

WEB_USE

US Cutsheet PDF Catalog Link <http://www-public.tnb.com/contractor/docs/stakon.pdf>

Features

Quick, reliable method of connection to terminal blocks and boards without the use of tools. Unique construction of the female disconnect offers long-term dependability.

General

Disconnect Type	Female - 187 Series
Insulation Type	Non-Insulated
Terminal Series	BD
Material	Brass
Finish	Electro -Tin Plated
Color	Metallic
Wire Range	16-14
Tab Size	.187 x .032

Dimension Information

Stock Thickness	.03
A (inches)	.64
B (inches)	.23

Specifications

Temperature Rating	150°C
Voltage Rating	600V
Flammability Rating	UL 94 V-0

Tooling

Tool Charts	Available on Website
Application Tools	WT111M, WT112M, ERG4002, WT2000
Recommended Tool	ERG4002

Packaging

T&B Order Multiple	100
T&B Inner Pack	100
Package in Units	500
Package Type	Standard
T&B Sold in UOM	Each
T&B Weight Per UOM	2.5 lbs. per 1000
Alternate Package Qty	BD183

Application Support

Overview	Available on Website
Wire Guide Tables	Available on Website

Certifications

RoHS Compliance Yes

Certifications



File Nbr:
E66716

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com