



Armored Cable/Flexible Metal Conduit Fittings

T&B Catalog Number:

325

UPC Number:

78621000325

Status:

Active

Description:

3/4 Inch. Tite-Bite 90 Degree Connector, Steel-Electro Zinc Plated.

Features

The angle clip gives secure mechanical grip that tightens under tension or vibration

Throat is long enough to install in cast housing knockouts.

Application

For use with Armored Cable and Flexible Metal Conduit.

To connect and effectively bond armored cable or flexible metal conduit to a box or an enclosure.

General

Trade Size (inches)

3/4

Material

Steel

Finish

Electro Zinc Plated

Dimension Information

Dimension A (inches)

2 1/8

Dimension B (inches)

2 1/8

Dimension C (inches)

1/2

Knockout Size (inches)

1/2

Cable Opening-Minimum (inches)

0.906

Cable Opening-Maximum (inches)

1.093

Specifications

3dmodel

Available on Website

Packaging

T&B Inner Pack

10

Package in Units

50

T&B Sold in UOM

Each

T&B Weight Per UOM

29.38 lbs. per 100

Certifications

RoHS Compliance

No

Certifications



File Nbr:

E 23018

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com