



Rigid/IMC Conduit Fittings

T&B Catalog Number:

130-TB

UPC Number:

78621000130

Status:

Active

Description:

3 1/2 in. Malleable Iron Bushing. For use with Rigid/IMC Conduit.

Features

Smoothly rounded shoulder covers end of conduit; broad flange covers knockout hole.

High ribs make tightening easy with fingers or with wrench.

Locknut-type base gives improved bonding and resist loosening under conditions of vibration.

Application

For use with rigid/IMC conduits

General

Trade Size (inches)

3 1/2

Material

Malleable Iron

Dimension Information

Dimension A (inches)

4 3/8

Dimension B (inches)

15/16

Specifications

3dmodel

Available on Website

Packaging

T&B Inner Pack

5

Package in Units

10

T&B Sold in UOM

Each

T&B Weight Per UOM

83.5 lbs. per 100

Application Support

T&B Sales Drawings

wsd-000019

Notes

Availabe with DURA-PLATE Finish

Certifications

RoHS Compliance

Yes

Certifications



File Nbr:

E 23018

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com