



Splice Connector T&B Catalog Number:

UPC Number: 2RZZ
78621080024
Status: Active
Description:

Insulated Nylon Aircraft Splice Connector For Wire Range 26-22 Length 1.22 Diameter .15, Yellow

WEB_USE

US Cutsheet PDF Catalog Link <http://www-public.tnb.com/contractor/docs/stakon.pdf>

Features

Nylon insulated splices meet or exceed the requirements of MIL-T-7928. These splices are color-coded according to wire size.



General

Insulation Type	Insulated Nylon
Terminal Series	RZZ
Material	Copper
Finish	Electro -Tin Plated
Color	Yellow
Wire Range	26-22

Dimension Information

Stock Thickness	.02
A (inches)	1.22
B (inches)	.15

Specifications

Temperature Rating	105°C
Voltage Rating	600V
Flammability Rating	UL 94 V-2

Tooling

Tool Charts	Available on Website
Application Tools	WT1452
Recommended Tool	ERG4006

Packaging

T&B Order Multiple	50
T&B Inner Pack	50
Package in Units	250
Package Type	Standard
T&B Sold in UOM	Each
T&B Weight Per UOM	1 lbs. per 100

Application Support

Overview	Available on Website
Wire Guide Tables	Available on Website

Certifications

RoHS Compliance	Yes
-----------------	-----

Certifications



File Nbr:
E9809

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com