



Armored Cable/Flexible Metal Conduit Fittings

T&B Catalog Number:

270

UPC Number:

78621000270

Status:

Active

Description:

3/4 in. Malleable Iron Squeeze Connector-90 degree.

Features

Cap lifts off by simply loosening screws part way, only two screws to tighten.

Application

For use with Armored Cable and Flexible Metal Conduit.

General

Trade Size (inches)	3/4
Material	Malleable Iron
Finish	Zinc Plate

Dimension Information

Dimension A (inches)	1 7/8
Dimension B (inches)	1 3/4
Dimension C (inches)	1 13/16
Knockout Size (inches)	3/4
Cable Opening-Minimum (inches)	1.000
Cable Opening-Maximum (inches)	1.125

Packaging

T&B Inner Pack	10
Package in Units	50
T&B Sold in UOM	Each
T&B Weight Per UOM	23.81 lbs. per 100

Certifications

RoHS Compliance	Yes
-----------------	-----

Certifications



File Nbr:
E 23018

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com