



## Splice Connector T&B Catalog Number:

54807

## UPC Number:

78621054807

## Status:

Active

## Description:

Copper Two-Way Splice - Long Barrel for 2 AWG, 125/24 Die Code 33  
Brown

### Features

Two-way connectors provide high pullout values, are easy to insulate and provide a low-resistance connection of high quality and low installed cost.

### General

Style	Two-Way Long Barrel Splice
Material	Copper
Finish	Tin-Plated
Wire Size	#2 AWG
Wire Size Flex	125/24 = 50.4 kcmil
Die Color	Brown
Die Code	33

### Dimension Information

A (inches)	1.88
E (inches)	0.43

### Specifications

Voltage Rating	600V
----------------	------

### Packaging

T&B Inner Pack	25
Package in Units	250
T&B Sold in UOM	Each
T&B Weight Per UOM	3.96 lbs. per 100

### Application Support

T&B Instruction Sheets	ta00674-tb2
------------------------	-------------

### Certifications

RoHS Compliance	Yes
-----------------	-----

### Certifications



File Nbr:

Y

For further technical assistance, please contact us...

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
www.tnb.com

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email:techsupport@tnb.com