



Locking Fork Terminal T&B Catalog Number:

UPC Number:
Status:
Description:

A18-6FL
78621080664
Active

Non-Insulated Locking Fork Terminal For Wire Range 22-16 Stud Size #6, Metallic

WEB_USE

US Cutsheet PDF Catalog Link

<http://www-public.tnb.com/contractor/docs/stakon.pdf>

Features

Locking fork terminals have a specially designed tongue that lets them go on like a fork and stay on like a ring.

General

Insulation Type	Non-Insulated
Terminal Series	A
Material	Copper
Finish	Electro -Tin Plated
Color	Metallic
Wire Range	22-16
Stud Size	#6

Dimension Information

Stock Thickness	.03
A (inches)	.75
B (inches)	.25
C (inches)	.27
M (inches)	.59

Specifications

Temperature Rating	150°C
Voltage Rating	600V
Flammability Rating	UL 94 V-0

Tooling

Tool Charts	Available on Website
Application Tools	WT110M, WT111M, WT112M, WT2000, ERG4002
Recommended Tool	ERG4002

Packaging

T&B Order Multiple	100
T&B Inner Pack	100
Package in Units	500
Package Type	Standard
T&B Sold in UOM	Each
T&B Weight Per UOM	0.19 lbs. per 100
Alternate Package Qty	A221

Application Support

Overview	Available on Website
Wire Guide Tables	Available on Website

Certifications

RoHS Compliance Yes

Certifications



File Nbr:
E9809

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com